

FP494 / FP496 – Rack Mount Power Source

- Single and multiple output configurations
- Ruggedized construction
- Tailored MIL-STD-1399

Features

- Power Good LEDs for both input and output voltages
- Remote / local activate via IEEE, 802.3, 100 base FX
- Elapsed time meter



FP494

640 Watt Ruggedized 19" Rack Mount Dual Output Supply

- 28 V, 315 Watt isolated output
- 5.5 V, 325 Watt isolated output

Input Power

- 115 Vac, 1PH (MIL-STD-1399)
- 10 ms Hold-up time

FP496

575 Watt Ruggedized 19" Rack Mount Triple Output Supply

- 200 V, 250 Watt (600 Watt surge) isolated output
- 26 V, 225 Watt (300 Watt surge) isolated output
- 5.5 V, 100 Watt isolated output

Environmental

- Operational Temperature: 0°C to 50°C
- Internal fans

EMI

- MIL-STD-461E CE102, CS101, CS114, CS116, RE101, RE102, RS101, RS103