

ConverterPAC Description

ConverterPACs are the family of slide-in output assemblies used in [MegaPAC power supplies](#). There are currently 12 ConverterPACs available for use. Most ConverterPACs of the same length are interchangeable within a MegaPAC and between different AC input MegaPAC chassis. They can be added, moved, or changed as necessary. The type of ConverterPAC used in this slot is a QPAC(L).

QPAC (L = Non-RoHS; GL - RoHS)

The QPAC output assembly consists of a [VI-200 DC to DC converter](#) that converts the unregulated high voltage bus to the desired regulated output voltage. Each QPAC (L) can provide up to 200 Watts of output power, and booster QPACs can be added in parallel for more power. QPACs are fused with a PC-Tron, DC-rated, fast-acting fuse. An active preload ensures the DC to DC converter operates in its highest noise performance range. As the load on the module increases, the preload removes itself from the circuit. Ripple and common mode noise filters on the output reduce ripple under any load conditions to 10mV p-p or 0.15% whichever is greater. A number of options such as DC Power Good signal, and output voltage Trim potentiometer are available. All QPACs have overcurrent protection with automatic recovery when the overcurrent condition is removed. Over Voltage Protection (OVP) and Over Temperature Limiting (OTL) are available. Please note that for the QPAC (L) the output voltage from either output terminal to chassis should not exceed 500 Vdc, or peak. QPACs can only be used in the extended length MegaPACs.




Newer QPAC (L)s have Autosense. This feature automatically locally senses the output if remote sense is not used. To check if an output has the Autosense feature, measure the impedance from the + Out to + Sense and - Out to - Sense pins. If the impedance is 5 ohms, then the output has Autosense and does not require local sense jumpers. If a unit does not have Autosense, sense connections must be made. Please also note that newer QPAC (L)s have new outputs studs that are 1/8" longer to allow for multiple lugs. They are fully compatible with the original flanged nut ConverterPACs for use in parallel arrays. For further technical information about ConverterPACs, contact Applications Engineering at 1-800-927-9474.

Options available for QPAC (L/GL)

OPTIONS		AVAILABILITY
D	Power Good	OPTIONAL
T	Trim +/-10%	OPTIONAL
F*	Trim: +10%/-50%	OPTIONAL

* Note: Not available for 1st Gen 10V, 12V and 15V modules. For more details, contact Factory.

QPAC (L) Output and Connector Pin Identification



J2 REMOTE SENSE TRIM/SC & POWER GOOD

MATING HDWR:
HOUSING- MOLEX P/N: 39-01-0073
TERMINALS- MOLEX P/N: 39-00-0031
CRIMP TOOL MOLEX P/N: 57005-5000

7	+SENSE
6	-SENSE
5	TRIM
4	Vcc IN
3	POWER GOOD
2	POWER GOOD INVERTED
1	SIGNAL GROUND

Output connector kits (optional) for your MegaPAC supply are available for purchase from Westcor:

	Part Number
Single phase input	19-130040
Three phase input	19-130041

For more details about any Westcor products, contact the factory at 1-800-735-6200 or go to our website at

www.vicorpower.com

