


VICOR CONFIDENTIAL

THIS DOCUMENT AND THE DATA DISCLOSED HEREIN OR HERewith IS NOT TO BE REPRODUCED, USED, OR DISCLOSED IN WHOLE OR IN PART TO ANYONE WITHOUT PERMISSION OF VICOR CORP.

| REV. | DESCRIPTION | DATE | APPROVED |
|------|----------------------|----------|----------|
| 1 | RELEASED PER E060461 | 02/01/06 | PEI MB |



- NOTES:
1. ASSEMBLY TO BE FREE OF NICKS.
 2. WINDINGS TO BE EVENLY SPACED.
 3. RoHS COMPLIANT, LEAD FREE PER CST-0001 LATEST REVISION, MAGNETICS SECTION.
 4. GENERAL WORKMANSHIP STANDARDS FOR MAGNETIC COMPONENTS PER WS-0002.
 5. \diamond DENOTES CRITICAL CHARACTERISTIC FOR LOT INSPECTION.

| | | | | | | |
|----------|---------|--------------|----------------|-------------|---------|-----------------|
| PINS 1&2 | 4 | PRI. | 8T OF #29 AWG. | 101 - 187 | 40 - 50 | 100 KHZ @ 1 VAC |
| PINS 3&4 | 3 | PRI. | 8T OF #29 AWG. | 101 - 187 | 40 - 50 | |
| PINS 5&6 | 3 | 1 SEC. | 8T OF #29 AWG. | 101 - 187 | 40 - 50 | |
| ITEM NO. | WINDING | NO. OF TURNS | IND.(uH) | DC RES (mΩ) | TEST | |

| | |
|---|-----------------|
| DRAWN BY | DATE |
| P.E.IENI | 11/07/05 |
| UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES - TOLERANCES ARE: | |
| FRACTIONS | DECIMALS ANGLES |
| *1/64 | .XX = +.01 ±1° |
| | .XXX = +.005 |
| THIRD ANGLE PROJECTION | |
| | |
| DO NOT SCALE DRAWING | |

VICOR

IND TOR PR BUS 3W ASSY DWG

| | | | |
|-------|----------|---------|------|
| SIZE | FSCM NO. | DWG NO | REV |
| B | 67131 | 29775 | 1 |
| SCALE | 4:1 | SHEET 1 | OF 1 |